

USAGE

Chrysanthos 3D Trailing Glazes H are a lead-free thick textured trail-able glaze designed for creating raised linear decoration.

The 3D Trailing Glazes H can be used on bisque, in conjunction with underglaze decoration, or on top of unfired glaze. They can be left unglazed or may be coated with coloured or clear glaze.

Chrysanthos 3D Trailing Glazes H achieve stability and versatility, without cracking and come in a convenient nozzle squeeze bottle.

To create more colours than those available, colours may be intermixed. This is achieved by squeezing colours to be mixed into a pallet and mixing with a clean brush or pallet knife. The mixed colour may then be scooped back into a clean applicator bottle.

APPLICATION

Shake the applicator bottle well and always test on paper first to ensure 3D Trailing Glaze flows correctly before attempting to decorate ware.

If glaze appears too thick, add a few drops of clean water and shake to combine thoroughly.

If applicator nozzle is blocked, remove and wash in hot water using paper clip wire to dislodge blockage. Dry nozzle before reattaching it to the bottle.

To apply, gently squeeze the bottle with the applicator tip above (and not touching) the ceramic surface.


PHYSICAL DATA

The Chrysanthos 3D Trailing Glazes H may be fired between cone 4 (1,186°C) and cone 8 (1,263°C) without significant flattening of the raised decoration.



Chrysanthos 3D Trailing Glazes

Colouring → Glazing → Firing Process



GW = Greenware

BW = Bisqueware

UG = Underglazes

OS = One Strokes

3D = 3D Trailing Glazes